



## LBFS

Point level detection based on frequency sweep technology

LBFS-#####.0

### Technical data

#### ATEX II 1D Ex ta IIC T100 °C Da

Maximum values for barrier selection, $U_i$	100 mA
Degree of protection for cable accessories	IP 67
Temperature class T100 °C	-40 < Tamb < 85 °C -25 < Tamb < 70 °C , with cable sensor

#### ATEX II 1G Ex ia IIC T4/T5

Maximum values for barrier selection, $U_i$	30 V DC
Maximum values for barrier selection, $I_i$	100 mA
Maximum values for barrier selection, $P_i$	750 mW
Internal capacitance, $C_i$	43 nF For versions with cable outlet add 0.17 nF/meter for cable lengths above 5 meters
Internal inductance, $L_i$	10 µH For versions with cable outlet add 0.27 µH/meter for cable lengths above 5 meters
Recommended barrier for output type PNP	PROFSI3-B25100-ALG-LS
Temperature class, T1 ... T4	-40 < Tamb < 85 °C
Temperature class, T1 ... T5	-40 < Tamb < 74 °C -25 < Tamb < 70 °C , with cable sensor

#### ATEX II 3G Ex nA IIC T4/T5

Voltage supply range, $U_n$	30 V DC , max.
Current rating, $I_n$	100 mA , max.
Degree of protection for cable accessories	IP 67
Temperature class, T1 ... T4	-40 < Tamb < 85 °C
Temperature class, T1 ... T5	-40 < Tamb < 74 °C -25 < Tamb < 70 °C , with cable outlet

#### Compliance and approvals

EMC Emission	EN 61326, installed in a closed metal tank
EMC Immunity	EN 61326, installed in a closed metal tank
Hygiene	Refer to section "Compliance and approvals"
Railway applications	EN 50155
Safety	cULus listed, E365692 WHG (overfill, leakage)
Marine	Refer to section "Compliance and approvals"
Explosion protection	ATEX II 1D Ex ta IIC T100 °C Da ATEX II 1G Ex ia IIC T4/T5 Ga ATEX II 3G Ex nA IIC T4/T5 Gc
Pharma	Refer to section "Compliance and approvals"

# LBFS

Point level detection based on frequency sweep technology

LBFS-#####.0

## Operating conditions

Ordering key	Process connection	BCID	Continuous		Temporary (t < 1 h)	
			Process temperature @ Tamb < 50 °C	Process pressure	Process temperature max. @ Tamb < 50 °C	Process pressure @ Process temperature max.
			(° C)	(bar)	(° C)	(bar)
LBFS-##1###.#	G 1/2 A ISO 228-1 BSC	G07	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##2###.#	G 3/4 A ISO 228-1	G10	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##3###.#	G 1 A ISO 228-1	G11	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##4###.#	G 1/2 A hygienic	A03	-40 ... 115	-1 ... 10	135	-1 ... 5
LBFS-##5###.#	G 1/2 A ISO 228-1 for reverse assembly (in-shell thread)	T10	-40 ... 85	-1 ... 100	N/A	N/A
LBFS-##6###.#	3/4-14 NPT	N03	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##7###.#	M18 x 1 ISO 261 / ISO 965	M11	-40 ... 115	N/A	N/A	N/A
LBFS-##A###.#	G 1/2 A DIN 3852-E, NBR gasket	G51	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##B###.#	G 1/2 A DIN 3852-E, FKM (Viton®) gasket	G51	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##E###.#	G 1/2 A DIN 3852-E, FKM (Viton®) gasket, with cooling neck	G51	-40 ... 150	-1 ... 100	N/A	N/A
LBFS-##G###.#	G 1/2 A ISO 228-1 BSC, with cooling neck, not applicable for mounting with ZPW1-7x1	G07	-40 ... 150	-1 ... 100	N/A	N/A
LBFS-##J###.#	G 1/2 A hygienic, high temperature, with cooling neck	A03	0 ... 150	-1 ... 10	N/A	N/A
LBFS-##K###.#	G 1/2 A hygienic, length 82 mm	A03	-40 ... 115	-1 ... 100	135	-1 ... 100
LBFS-##L###.#	G 1/2 A hygienic, sliding connection, length 250 mm	A03	-40 ... 200	-1 ... 5	N/A	N/A
LBFS-##M###.#	1/2-14 NPT, with cooling neck	N02	-40 ... 150	-1 ... 100	N/A	N/A
LBFS-##N###.#	1/2-14 NPT	N02	-40 ... 115	-1 ... 100	135	-1 ... 100

For further information on permissible process and ambient temperatures, please refer to the operating instructions.

# LBFS

Point level detection based on frequency sweep technology

LBFS-#####.0

## Compliance and approvals


Ordering key	Process connection	BCID	EN 1935/2004 EN 10/2011 EN 2023/2006	FDA	3-A	EHEDG EL-Class I	USP Class VI	DNV GL	Lloyd's Register	CCS	WHG (overfill, leakage)
LBFS-##1###.#	G 1/2 A ISO 228-1 BSC	G07					■	■	■	■	■
LBFS-##2###.#	G 3/4 A ISO 228-1	G10					■	■	■	■	■
LBFS-##3###.#	G 1 A ISO 228-1	G11					■	■	■	■	■
LBFS-##4###.#	G 1/2 A hygienic	A03	■	■	■	■	■	■	■	■	■
LBFS-##5###.#	G 1/2 A ISO 228-1 for reverse assembly (in-shell thread)	T10					■	■	■	■	■
LBFS-##6###.#	3/4-14 NPT	N03					■	■	■	■	■
LBFS-##7###.#	M18 x 1 ISO 261 / ISO 965	M11					■	■	■	■	■
LBFS-##A###.#	G 1/2 A DIN 3852-E, NBR gasket	G51					■	■	■	■	■
LBFS-##B###.#	G 1/2 A DIN 3852-E, FKM (Viton®) gasket	G51					■	■	■	■	■
LBFS-##E###.#	G 1/2 A DIN 3852-E, FKM (Viton®) gasket, with cooling neck	G51					■			■	■
LBFS-##G###.#	G 1/2 A ISO 228-1 BSC, with cooling neck	G07					■			■	■
LBFS-##J###.#	G 1/2 A hygienic, high temperature, with cooling neck	A03	■	■	■						
LBFS-##K###.#	G 1/2 A hygienic, length 82 mm	A03	■	■						■	■
LBFS-##L###.#	G 1/2 A hygienic, sliding connection, length 250 mm	A03	■	■		■				■	■
LBFS-##M###.#	1/2-14 NPT, with cooling neck	N02								■	■
LBFS-##N###.#	1/2-14 NPT	N02						■	■	■	■

Information on product characteristics may relate to defined product options.


The requirements of the respective 3-A Sanitary Standard will be only fulfilled in combination with appropriate mounting accessories. Those are marked with the 3-A logo.

The EHEDG certification is only valid in combination with appropriate mounting accessories. Those are marked with the "EHEDG Certified" logo.


## Dimensional drawings (mm)



G 1/2 A ISO 228-1 BSC (BCID: G07)



G 3/4 A ISO 228-1 (BCID: G10)




G 1 A ISO 228-1 (BCID: G11)

# LBFS


Point level detection based on frequency sweep technology

LBFS-#####.0


## Dimensional drawings (mm)




G 1/2 A hygienic (BCID: A03)




G 1/2 A ISO 228-1 for reverse assembly (in-shell thread) (BCID: T10)




3/4-14 NPT (BCID: N03)



M18 × 1 ISO 261 / ISO 965 (BCID: M11)



G 1/2 A DIN 3852-E (BCID: G51)




1/2-14 NPT (BCID: N02)

# LBFS


Point level detection based on frequency sweep technology

LBFS-#####.0


## Dimensional drawings (mm)



G 1/2 A ISO 228-1 BSC with cooling neck  
(BCID: G07)



G 1/2 A hygienic, 82 mm length (BCID: A03)




G 1/2 A hygienic, sliding connection, 250 mm length, including compression ring kit ZPX1-006 (BCID: A03)

# LBFS


Point level detection based on frequency sweep technology

LBFS-#####.0


## Dimensional drawings (mm)



1/2-14 NPT with cooling neck (BCID: N02)




G 1/2 A DIN 3852-E with cooling neck (BCID: G51)




G 1/2 A hygienic, high temperature, with cooling neck (BCID: A03)


## Housing



Connector M12-A, 4-pin, polycarbonate (with LED)



Cable outlet, 4-wire, 5 m length



Connector M12-A, 4-pin, stainless steel (without LED)

# LBFS

Point level detection based on frequency sweep technology

LBFS-#####.0

## Electrical connection

Output type	Electrical connection	Equivalent circuit	Function	Pin assignment
PNP			+Vs	1
			SW1, Normally open (NO)	4
			SW1, Normally closed (NC)	2
			GND (0 V)	3
			+Vs	BN
			SW1, Normally open (NO)	BK
SW1, Normally closed (NC)	WH			
GND (0 V)	BU			
NPN			+Vs	1
			SW1, Normally open (NO)	4
			SW1, Normally closed (NC)	2
			GND (0 V)	3
			+Vs	BN
			SW1, Normally open (NO)	BK
SW1, Normally closed (NC)	WH			
GND (0 V)	BU			

## Ordering information

Ordering key - Configuration possibilities see website

Product	LBFS	-	#	####	.	#	#	#	#
Level switches	LBFS								
<b>Compliance and approvals</b>									
Standard				0					
IECEX / ATEX ia				1					
IECEX / ATEX ta				2					
ATEX nA				3					
IECEX / ATEX ia + ta				4					
cUL listed, E365692				A					
EAC (TR CU 020/2011)				B					
<b>Electrical Connection</b>									
M12-A, 4-pin, polycarbonate (with LED)									1
Cable outlet 5 m, 4-wire, PVC									2
M12-A, 4-pin, stainless steel (without LED)									3



# LBFS

Point level detection based on frequency sweep technology

LBFS-#####.0

## Ordering information

Ordering key - Configuration possibilities see website

LBFS - # ##### . # # # #

### Process Connection

G 1/2 A ISO 228-1 (G07)	1
G 3/4 A ISO 228-1 (G10)	2
G 1 A ISO 228-1 (G11)	3
G 1/2 A hygienic (A03)	4
G 1/2 A ISO 228-1 for reverse assembly (in-shell thread) (T10)	5
3/4-14 NPT (N03)	6
M18x1 (M11)	7
G 1/2 A DIN 3852 form E, NBR gasket (G51)	A
G 1/2 A DIN 3852 form E, FKM (Viton®) gasket (G51)	B
G 1/2 A ISO 228-1 with cooling neck (G07)	G
G 1/2 A hygienic, high temperature, with cooling neck(A03)	J
G 1/2 A hygienic, length 82 mm (A03)	K
G 1/2 A hygienic, sliding connection, length 250 mm (A03)	L
1/2-14 NPT (N02)	N
1/2-14 NPT with cooling neck (N02)	M
G 1/2 A DIN 3852 form E, FKM (Viton®) gasket, with cooling neck (G51)	E

### Process connection material

Stainless Steel 1.4301 - AISI 304	1
Stainless Steel 1.4404 - AISI 316L	2

### Output Configuration

PNP output	1
NPN output	2

### Configuration

Factory settings	0
Customer-specific	C

(1) Including gasket ZPX3-14B0 (glass/aramide fiber with NBR)